

## High Energy Waveplates

### Typical Items\*

Wavelength, nm	Product ID		
	Mount size, Ø12.7 x 6 mm	Mount size, Ø25.4 x 6 mm	Mount size, Ø25.4 x 6 mm
	$\lambda/2$ retardation, clear aperture >8 mm	$\lambda/2$ retardation, clear aperture >18 mm	$\lambda/4$ retardation, clear aperture >18 mm
266		2-CPW-TSO-L2-0266	2-CPW-T4O-L4-0266-W
343	2-CPW-TFO-L2-0343-S	2-CPW-TFO-L2-0343-W	2-CPW-TTO-L4-0343-W
355	2-CPW-TFO-L2-0355-S	2-CPW-TFO-L2-0355-W	2-CPW-TSO-L4-0355-W
400	2-CPW-TFO-L2-0400-S	2-CPW-TFO-L2-0400	2-CPW-TSO-L4-0400
515	2-CPW-TZO-L2-0515-S	2-CPW-TFO-L2-0515	2-CPW-TSO-L4-0515
532	2-CPW-TZO-L2-0532-S	2-CPW-TFO-L2-0532	2-CPW-TFO-L4-0532
780			2-CPW-TFO-L4-0780
800	2-CPW-TZO-L2-0800-S	2-CPW-TZO-L2-0800	2-CPW-TFO-L4-0800
1030	2-CPW-TZO-L2-1030-S	2-CPW-TZO-L2-1030	2-CPW-TFO-L4-1030
1064	2-CPW-TZO-L2-1064-S	2-CPW-TZO-L2-1064	2-CPW-TFO-L4-1064

\* Customized solutions are available on request.