

## Mid-IR Waveplates

### Typical Items

Wavelength, nm	Product ID	
	$\lambda/2$ retardation, clear aperture >10 mm	$\lambda/4$ retardation, clear aperture >10 mm
2940	2-IRPW-ZO-L2-2940-C	2-IRPW-ZO-L4-2940-C
3000	2-IRPW-ZO-L2-3000-C	2-IRPW-ZO-L4-3000-C
3500	2-IRPW-ZO-L2-3500-C	2-IRPW-ZO-L4-3500-C
4000	2-IRPW-ZO-L2-4000-C	2-IRPW-ZO-L4-4000-C
4500	2-IRPW-ZO-L2-4500-C	2-IRPW-ZO-L4-4500-C
5000	2-IRPW-ZO-L2-5000-C	2-IRPW-ZO-L4-5000-C
5500	2-IRPW-ZO-L2-5500-C	2-IRPW-ZO-L4-5500-C
6000	2-IRPW-ZO-L2-6000-C	2-IRPW-ZO-L4-6000-C
6500	2-IRPW-ZO-L2-6500-C	2-IRPW-ZO-L4-6500-C
7000	2-IRPW-ZO-L2-7000-C	2-IRPW-ZO-L4-7000-C
7500	2-IRPW-ZO-L2-7500-C	2-IRPW-ZO-L4-7500-C
8000	2-IRPW-ZO-L2-8000-C	2-IRPW-ZO-L4-8000-C
9000	2-IRPW-ZO-L2-9000-C	2-IRPW-ZO-L4-9000-C

### Uncoated

2940	2-IRPW-ZO-L2-2940	2-IRPW-ZO-L4-2940
3000	2-IRPW-ZO-L2-3000	2-IRPW-ZO-L4-3000
6000	2-IRPW-ZO-L2-6000	2-IRPW-ZO-L4-6000